

>



Model Number: SBM3AE11

Clean Storm 120 Volt Hour Meter Panel Mount (self install) SBM3AE11

Manufacturer: Clean Storm

## Carpet Cleaners Hour Meter

120 Volt AC Operation (2in hole diameter, 2 3/4in flange) Round Hour Meter  
This hour meter operates on 120 Volts AC and is a general purpose non-resetable hour meter. For use on any 120 volt equipment where hours of operation need to be monitored for maintenance such as carpet clean machines, cavity and wall pressurization equipment or any other AC system. These meters are 100% tested at the factory prior to shipment.

### Note:

Pumptec regulators are to have the piston lubricated every 250 hours

Pumptec Pumps are to have the head rebuilt every 500 hours

Vacuum motors are to have carbon brushes changed out every 500 to 750 hours depending on model

This is part of regular maintenance and is not covered under the original factory warranty or extended warranty.

The only way you will be able to keep track of the hours is to install an hour meter on the machine.

They will have either 0.1 or 0.2 hours on them depending on the random quality control test selection process. This is done to insure that a quality meter is being shipped.

Reading 99999.9 hours Accuracy 1/10th hour Quartz Weight 2 Ounces  
Voltage Supply 120 Volts AC Temperature Range -4 to 149 Fahrenheit; -20C to 65C  
Power Consumption 2 Watts Dimensions OD 2.77 Depth Behind front meter flange to end of spade lug - 1.62 inches Hole size

Can be panel mounted with the on front ring or by using the square support ring shown on above left side of photo. It has a "click and seal" set up. Hard to explain but as you slide up the back wall of the meter, it click, click, click to squeeze up against the back wall to hold meter in place.

>

. Optional Labor to install on your equipment \$40.00  
Please note to do the installation at SteamBrite you must be purchasing a piece of equipment that is shipping from SteamBrite San Antonio TX

Photo below is an older photo and these no longer include the 3 hole mounting, rather the clip in from the rear instead.

---

*Availability: This product was added to our catalog on Wednesday 10 October, 2012*